section C

272

## VIBRATING TABLES

STANDARDS: EN 12390-2 / BS 1881:108 / UNI 6127

Used for the compaction of concrete specimens in laboratory, they are manufactured from rugged steel sheet.

Equipped with motor-vibrator having 3000 vibrations-minute, it is possible to vary the vibration intensity by acting on the excentric masses. The height of the table is 410 mm.

All the vibrating tables accept the clamping device, pedal swith or

control panel (see accessories). Power supply: 230 V lph 50 Hz

Models	Table dimensions mm	Power W	Weight kg	*Clamping device
C278	600×400	180	60	C281-01
C278-01	800×400	180	85	C281-02
C278-02	800×800	180	115	C281-03
C279	1100×550	180	145	C281-04

\*The clamping device is used to fix the moulds to the table during the vibrating action.





Similar to the above Vibrating Tables, suitable for site and laboratory use, they accept ONE GANG cube moulds (max. 200 mm side) or cylinders max. I 60x320mm, both plastic and metal made.

Supplied complete with elastic bands to fix the mould to the table. Table dimensions: 400×300mm, height 200mm

Weight: 16 kg

## MODELS: **C281N**


Vibrating table, portable, 12V dc Suitable for site use, where no electric supply is available.

Lightweight and small sized, it can be handled by one person and easily stored in the car trunk.

Supplied complete with On/Off switch and connector for the vehicle cigar lighter

## C282 Vibrating table

Similar to mod, C281N, but for laboratory use Power supply: 230V lph 50Hz 110W





C278 with moulds C253-01







